



Servicing Outdoor Power Equipment Dealers Since 1984
8 McFadden Road ☎ Easton, PA 18045 ☎ (800) 942-2326 ☎ <https://shop.cadcodist.com/>

Stinger Information

Quad AER Wheel Motors & Hubs

Seal Kits

Seal Kit for Parker Wheel Motor – SK000091

If it has a Danfoss Wheel Motor - No seal kit available

Wheel Motors on QA3600

	<u>Left Side</u>	<u>Right Side</u>
QA3600 - GEN 1 - Ser 00000 - 39999	40-1361-2	40-1361
QA3600 - GEN 2 - Ser 40000 - 49999	40-1361-2	40-1361
QA3600 - GEN 3 - Ser 50000 - up	40-1361-3	40-1361-3 (Same motor used on both sides)

Wheel Hubs

Wheel hubs come with studs already installed (Some hubs have non-replaceable studs)

New hubs for QA3000's don't have keyways. (Wheel motor is designed for keyed or keyless hubs)

Proper torque on installation and maintenance schedule is imperative!

20-2433 – QA3000 Gen 1 units (Serial 29999 and below) Non-replaceable studs

20-3510 – QA3000 Gen 2 & 3 ((Serial 30000 to current)

20-1550 – QA3600 All

30-3509 – Wheel Studs

Service Information

The Lug Nut torque on QA's is 98 ft-lbs

The Hub Castle Nut torque on QA's is 200 ft-lbs (Spec is 175 – 255 ft-lbs)

Hubs should be retorqued after the first 15hrs of use and every 200hrs thereafter.